

	Hämofilter	max. Blutfluss [ml/min]	Priming-Volumen [ml]	Membran-Oberfläche [m²]	max. TMP [mmHg]	Material Filtermembran	max. Molekülgröße [Dalton]	Filtrationsrate [ml/h/mmHg]	Ultrafiltration [ml/min] (bei 200 ml/min + 200 mmHg)	Anschlüsse Blutseitig	Anschlüsse Filtratseitig
Terumo	HC05	500	34,0	0,50	500	Polysulfon	65000			1/4"-Konnektor	1/2"-Hansen
	HC11	500	67,0	1,10	500	Polysulfon	65000			1/4"-Konnektor	1/2"-Hansen
Getinge	BC 20 plus	100	17,0	0,22	600	Polyarylethersulfon				Pos-Lock male	LuerLock female
	BC 60 plus	400	65,0	0,70	600	Polyarylethersulfon				Pos-Lock male	Luer-Lock female
	BC 140 plus	500	98,0	1,35	600	Polyarylethersulfon				Pos-Lock male	Luer-Lock female
Mintech (Hemocor)	HPH Junior		8,0	0,09	500	Polysulfon	65000			Luer-Lock male	Luer-Lock female
	HPH Mini		14,0	0,07	500	Polysulfon	65000			Luer-Lock male	Luer-Lock female
	HPH 400		34,0	0,30	500	Polysulfon	65000			1/4"-Konnektor	1/4"-Konnektor
	HPH 700		56,0	0,71	500	Polysulfon	65000			1/4"-Konnektor	1/4"-Konnektor
	HPH 1000		84,0	1,06	500	Polysulfon	65000			1/4"-Konnektor	1/4"-Konnektor
	HPH 1400		100,0	1,30	500	Polysulfon	65000			1/4"-Konnektor	1/4"-Konnektor
LivaNova	DHF02	500	30,0	0,25	500	Polyethersulfon	65000	16,00		Pos-Lock male	1/4"-Konnektor
	DHF06	500	60,0	0,68	500	Polyethersulfon	65000	31,00		Pos-Lock male	1/4"-Konnektor
	SH14	500	80,0	1,35	500	Polyethersulfon	65000	61,00		Pos-Lock male	1/2"-Hansen
Freelife	HF 0,2		15,0	0,20	500	Micro-Undulated Polysulfon		7,00		Luer-Lock male	Luer-Lock female
	HF 0,3		21,0	0,30	600	Polyethersulfon		14,00		Pos-Lock male	Luer-Lock female
	HF 0,7		49,0	0,70	600	Polyethersulfon		32,00		Pos-Lock male	Luer-Lock female
	HF 3		65,0	1,30	500	Polyethersulfon		54,00		Pos-Lock male	1/2"-Hansen
	HF 6		80,0	1,60	500	Polyethersulfon		68,00		Pos-Lock male	1/2"-Hansen

Medica	<b>D025</b>		2,5	0,02	600	Polysulfon	50000	0,32		Luer-Lock female	Luer-Lock female
	<b>D050</b>		5,0	0,08	600	Polysulfon	50000	1,30		Luer-Lock male	Luer-Lock female
	<b>D100</b>		10,0	0,15	600	Polysulfon	50000	3,00		1/4"-Konnektor	1/4"-Konnektor
	<b>D150</b>		19,0	0,25	600	Polysulfon	50000	5,50		Pos-Lock male	Luer-Lock female
	<b>DP03HC</b>		21,0	0,30	600	Polyethersulfon	50000	14,00		Pos-Lock male	Luer-Lock female
	<b>DP07HC</b>		49,0	0,70	600	Polyethersulfon	50000	32,00		Pos-Lock male	Luer-Lock female
	<b>DP09HC</b>		57,0	0,90	600	Polyethersulfon	50000	41,00		Pos-Lock male	Luer-Lock female
	<b>DP12HC</b>		75,0	1,20	600	Polyethersulfon	50000	55,00		Pos-Lock male	Luer-Lock female
	<b>DP15HC</b>		87,0	1,50	600	Polyethersulfon	50000	63,00		Pos-Lock male	Luer-Lock female